REVISION HISTORY			
REV	DATE	BY	DESCRIPTION
E	11MAR2025	VRG/SAK	PRN: P2025-0363







NOTES

A. THE FOLLOWING SCREWS MAY BE USED TO MOUNT THE HANDLE - M5 OR #10 SCREWS WITH THE FOLLOWING HEAD STYLES - HEX SLOTTED HEAD, PAN HEAD, FILLISTER HEAD, BINDING HEAD, ROUND HEAD, HEX FLANGE HEAD AND HEX WASHER HEAD.
B. HANDLES ARE BULK PACKAGED
C. INSTALLATION INSRTUCTIONS:
   1. DRILL PILOT HOLES AS SHOWN.
   2. MOUNT HANDLE USING M5 OR #10 SCREWS. (SCREWS ARE NOT PROVIDED)
   3. SNAP COVER ONTO HANDLE.
D. B8-63-3-P BULK PACK AS FOLLOWS: IN A 1-03-11 BOX, PACK 4 LAYERS OF 34 HANDLES EACH. WITH FIFTH LAYER HAVING 14 HANDLES, BAG 150 HANDLE COVERS AND PLACE ON THE FIFTH LAYER WITH THE HANDLES.
E. B8-63 IS SINGLE PACKAGE PER S-34 , TYPE I, CLASS A

NO.	ASSEMBLY PART NUMBER	TYPE OF COMPONENT	MATERIAL	COLOR
2	-	HANDLE	ABS/PC	BLACK
1	-	COVER	ABS/PC	BLACK
-	B8-63	ASSEMBLY	-	-
2	-	HANDLE	ABS/PC	BLACK
1	-	COVER	ABS/PC	BLACK
-	B8-63-3-P (SEE NOTE D)	ASSEMBLY	-	-
2	-	HANDLE	ABS/PC	BLACK
1	-	COVER	ABS/PC	BLACK
-	B8-63-3	ASSEMBLY	-	-

SURFACE AREA

VOLUME

PROPRIETARY ITEM

EXCEPT FOR USES EXPRESSLY GRANTED IN WRITING, INFORMATION DISCLOSED HEREON IS CONFIDENTIAL AND ALL RIGHTS, PATENT AND OTHERWISE, ARE RESERVED BY SOUTHCO, INC.

THIRD ANGLE PROJECTION

MILLIMETERS [IN]

TOLERANCES UNLESS OTHERWISE NOTED

ALL DIMENSIONS WITHOUT TOLERANCES ARE FOR REFERENCE ONLY.

PER ASME Y14.5M-2009

southco®
CONNECT·CREATE·INNOVATE

DESCRIPTION: FRONT MOUNT B8 HANDLE

SIZE	SYSTEM	DWG NO.
A4	NX	J-B8-63

DRAWN BY	DATE	SCALE	SHEET
SWD	21JAN1998	1:3	1 OF 1