REVISION HISTORY			
REV	DATE	BY	DESCRIPTION
C	06AUG2025	SSK/SAK	PRN: P2025-1329

FOR AN ASSEMBLY WITH A BLACK POLYESTER POWDER COATED CUP, PADDLE AND COVER: CHANGE THE LAST DIGIT OF THE PART NUMBER TO "5".
EXAMPLE: 64-10-111-55
LATCH, MOUNTING BRACKET AND NUT ARE SHIPPED SEPARATELY, BULK









PANEL PREPARATION

PART NUMBER	GRIP RANGE MIN.	GRIP RANGE MAX.	"A" MIN.	"A" MAX.	"T" MAX	PAWL STYLE
64-10-126-50	18.6	19.4	11.9	14.2	7.1	6
64-10-125-50	12.3	13.1			7.1	5
64-10-124-50	6	6.7			6.4	4
64-10-113-50	2.8	3.6			3.2	3
64-10-112-50	2	2.8	11.2	13.5	2.4	2
64-10-111-50	1.2	2	10.4	12.7	1.6	1

INSTALLATION INSTRUCTIONS
PREPARE A RECTANGULAR HOLE IN PANEL, AS SHOWN.
INSERT LATCH AND PLACE MOUNTING BRACKET OVER STUD.
SECURE BRACKET WITH THE MOUNTING NUT

MATERIAL AND FINISH
CUP PADDLE AND COVER: 304 STAINLESS STEEL, PASSIVATED PLUS SATIN BRUSHED FINISH.
SLIDE: GLASS REINFORCED NYLON, NATURAL.
PIN: 302 STAINLESS STEEL, PASSIVATED.
SPRINGS: 302 STAINLESS STEEL, PASSIVATED.
STUD: 304 STAINLESS STEEL, PASSIVATED.
MOUNTING BRACKET: 302 STAINLESS STEEL, PASSIVATED.
MOUNTING NUT: 304 STAINLESS STEEL, PASSIVATED WITH A NYLON INSERT

CPB NUMBER 2013-1045

PROPRIETARY ITEM
EXCEPT FOR USES EXPRESSLY GRANTED IN WRITING, INFORMATION DISCLOSED HEREON IS CONFIDENTIAL AND ALL RIGHTS, PATENT AND OTHERWISE, ARE RESERVED BY SOUTHCO, INC.

THIRD ANGLE PROJECTION
MILLIMETERS [IN]
TOLERANCES UNLESS OTHERWISE NOTED
ALL DIMENSIONS WITHOUT TOLERANCES ARE FOR REFERENCE ONLY.
PER ASME Y14.5M-2009

southco®
CONNECT·CREATE·INNOVATE

DESCRIPTION
No. 64 SMALL PADDLE LATCH WITH PLASTIC SLIDE FIRST BRACKET STYLE (FOR THIN PANELS)

SIZE	SYSTEM	DWG NO.
A3	NX	J-64-100-1

DRAWN BY	DATE	SCALE	SHEET
BMC/JSS	03NOV1994	1:1	1 OF 1